

Number of contacts

20

500 V
16 A

Han-
Modular

Identification

Wire cross section (mm²)

Part number
male female

Drawing
Dimensions in mm


Han-Modular®,
Han® EEE module,
Crimp terminal



Please order crimp contacts separately.

09 14 020 3001

09 14 020 3101



Contact arrangement (view from termination side)


Han E®,
Crimp contact,
gold plated contacts,
contact resistance ≤1 mOhm



0.14–0.37
0.5
0.75
1
1.5
2.5
4

09 33 000 6117
09 33 000 6122
09 33 000 6115
09 33 000 6118
09 33 000 6116
09 33 000 6123
09 33 000 6119

09 33 000 6217
09 33 000 6222
09 33 000 6215
09 33 000 6218
09 33 000 6216
09 33 000 6223
09 33 000 6221



Identification	Wire gauge	Stripping length
no groove	0.14-0.37 mm ² AWG 26-22	7.5 mm
no groove	0.5 mm ² AWG 20	7.5 mm
1 groove*	0.75 mm ² AWG 18	7.5 mm
1 groove	1 mm ² AWG 18	7.5 mm
2 grooves	1.5 mm ² AWG 16	7.5 mm
3 grooves	2.5 mm ² AWG 14	7.5 mm
wide groove	3 mm ² AWG 12	7.5 mm
no groove	4 mm ² AWG 12	7.5 mm

* on the back crimp collar


Han E®,
Crimp contact,
silver plated contacts,
contact resistance ≤1 mOhm



0.14–0.37
0.5
0.75
1
1.5
2.5
3
4

09 33 000 6127
09 33 000 6121
09 33 000 6114
09 33 000 6105
09 33 000 6104
09 33 000 6102
09 33 000 6106
09 33 000 6107

09 33 000 6227
09 33 000 6220
09 33 000 6214
09 33 000 6205
09 33 000 6204
09 33 000 6202
09 33 000 6206
09 33 000 6207



Identification	Wire gauge	Stripping length
no groove	0.14-0.37 mm ² AWG 26-22	7.5 mm
no groove	0.5 mm ² AWG 20	7.5 mm
1 groove*	0.75 mm ² AWG 18	7.5 mm
1 groove	1 mm ² AWG 18	7.5 mm
2 grooves	1.5 mm ² AWG 16	7.5 mm
3 grooves	2.5 mm ² AWG 14	7.5 mm
wide groove	3 mm ² AWG 12	7.5 mm
no groove	4 mm ² AWG 12	7.5 mm

* on the back crimp collar