


P1,P2: M-Y139C
 M-139C
 P3 : M-426E



⚠ * NOTE: All relevant materials are complied with RoHS directive .

1054		
P1		P2
1	_____	1
2	_____	2
3	_____	3
4	_____	4
5	_____	5
6	_____	6
7	_____	7
8	_____	8
9	_____	9
SHIELD	_____	SHIELD

No.	DESCRIPTION	Q'TY	Supplier
6	BLACK PVC TUBE ϕ 3.0*22mm	2	M304
	ALUMINUM FOIL 33*65mm	2	M309
	MOLDED PE COLOR TRANSPARENT		TWN
	MOLDED PVC BEIGE		M304
5	NON-UL 9C 28AWG, ALUM-MYLAR FOIL SHIELDING WITH DRAIN WIRE, OD 5.0, JACKET BEIGE,	L-20mm	M304
4	HEX-NUT 5*6.6mm	2	M95
3	MOLDED THUMBSCREW #4-40, LENGTH 46.5mm, BEIGE	4	M95
2	DB9 FEMALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	1	M108
1	DB9 MALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	1	M108

APPROVED		EX-011	Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm
CHECKED			
DRAWING			
DATE	04/JUL/07		
ITEM NO.			UNIT:mm

