

## Specification:

- Rated load 0.5A 30V DC
- Contact resistance 0.05Ω
- Insulation resistance 100MΩ
- Withstand voltage 250V AC 50Hz/min
- Life cycle 5,000 insertions
- Actuating force 3 to 30N
- Temperature -20°C to +70°C

