


E12317



Connection cable

VDOGH050MSS0010C02STG020MSS



Application	
Special feature	Halogen-free; Gold-plated contacts; Screened cable
Electrical data	
Operating voltage [V]	< 30 AC / < 36 DC
Max. current load total [A]	4; (...40 °C)
Operating conditions	
Ambient temperature [°C]	-25...85
Protection	IP 67
Mechanical data	
Weight [g]	652.5
Dimensions [mm]	14.5 x 14.5 x 48.5
Materials	PUR
Material nut	brass, nickel-plated / brass, nickel-plated
Remarks	
Pack quantity	1 pcs.

Electrical connection - plug

Connector: 1 x M12, straight; Moulded body: PUR; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.6 Nm; Shielded connection cable: screen connected



E12317




Connection cable

VDOGH050MSS0010C02STG020MSS

Electrical connection

Cable: 10 m, PUR, Halogen-free, lilac, shielded; 2 x 0.25 mm²

Connection



Core colours :

GN = green

RD = red

Electrical connection - socket

Connector: 1 x M12, straight; Moulded body: PUR; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.6 Nm; Shielded connection cable: screen connected

