

## MODLINK MSDD DATA INSERT

1×SUB-D25 female/male + 2×RJ45


RJ45; RJ45; SUB-D25

2 × RJ45, 8-pole metal, CAT5e (female/female)

1 × SUB-D25 (female/male)

### [Link to Product](#)

#### Illustration



Product may differ from Image

#### Approvals



#### General data

Dimensions H × W × D 88×51×21 mm

#### Insert 2

Article number 4000-68000-1600000

Operating voltage SUB-D: max. 125 V AC/150 V DC; RJ45: max. 48 V AC/DC; RJ12: max. 48 V AC/DC; USB: max. 30 V AC/DC; PS2: max. 30 V AC/DC; DVI: max. 40 V AC

Operating current SUB-D: max. 3 A; RJ45: max. 1 A; RJ12: max. 1 A; USB: max. 1 A; PS2: max. 1 A; DVI: max. 1.5 A

Connection cross section SUB-D: max. 0.5 mm<sup>2</sup> (AWG 20); PS2: max. 0.22 mm<sup>2</sup> (AWG 24)

Locking of ports SUB-D: UNC 4...40 bolt; RJ45: staple; RJ12: staple; USB: snap-in; PS2: snap-in

|                        |   |
|------------------------|---|
| Specification          | SUB-D: (DIN 41652/IEC 60807-1); RJ45: CAT5e (100 MHz - Mbit/s);<br>USB: 2.0/Type 2dB (max. 480 Mbit/s)    |
| Mounting depth mounted | SUB-D: approx. 32 mm; RJ45: approx. 32 mm; RJ12: approx. 32 mm;<br>USB: approx. 80 mm; PS2: approx. 32 mm |
| Dimensions H x W x D   | 88x51x21  |
| Shielded               | yes   |
| <b>Commercial data</b> |   |
| country of origin      | CZ  |
| customs tariff number  | 85369010  |
| minimum order quantity | 1   |