

LED LAMP YELLOW 12...60V



Figure similar

Model		
Type of light source		LED
Mounting type		others
Main circuit		
Operating voltage		
<ul style="list-style-type: none"> • with AC / at 50 Hz / Rated value / minimum 	V	12
<ul style="list-style-type: none"> • with AC / at 50 Hz / Rated value / maximum 	V	60
<ul style="list-style-type: none"> • with AC / at 60 Hz / Rated value / minimum 	V	12
<ul style="list-style-type: none"> • with AC / at 60 Hz / Rated value / maximum 	V	60
<ul style="list-style-type: none"> • for DC / Rated value / minimum 	V	12
<ul style="list-style-type: none"> • for DC / Rated value / maximum 	V	60
Appearance		
Color / of the light source		yellow
Product details		
Product component		
<ul style="list-style-type: none"> • diode 		Yes
<ul style="list-style-type: none"> • lamp transformer 		No
<ul style="list-style-type: none"> • Light source 		Yes
<ul style="list-style-type: none"> • series resistor 		No
Connections		
Type of electrical connection / for auxiliary circuit		others
Mechanical Design		
Mounting type		others



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/5TG80562>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/5TG80562/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=5TG80562

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015