

## T50R0PPM4



**Article Number: 111-04929**

**High Temp Tie, 8" Long, 25lb Tensile Strength, PP, Black, 1000/pkg**



Download drawing



Download spec sheet

### Base Data

**Local Order Number** T50R0PPM4

**Type** T50R

**Color** Black (BK)

- Features and Benefits**
- Polypropylene cable ties provide excellent resistance to chemicals and salts.
  - Inside serrations allow for strong hold on cables and wire bundles.
  - Head design provides high tensile strength with very low insertion force.
  - Bent tail ensures a quick and simple installation.

**Product Description** HellermannTyton standard cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

**Short Description** High Temp Tie, 8" Long, 25lb Tensile Strength, PP, Black, 1000/pkg

### Product Dimensions

**Minimum Tensile Strength (Imperial)** 25.0 lbs

**Minimum Tensile Strength (Metric)** 111.0 N

**Length L (Imperial)** 8.0 "

**Length L (Metric)** 202.0 mm

**Fixation Method** None

**Identification Plate Position** none

**Releasable Closure** No

**Tie Closure** plastic pawl

**Variant** Inside Serrated

**Width W (Imperial)** 0.19 "

**Width W (Metric)** 4.8 mm

**Bundle Diameter Min. (Imperial)** 0.5 "

**Bundle Diameter Min. (Metric)** 12.7 mm

**Bundle Diameter Max. (Imperial)** 1.75 "

**Bundle Diameter Max. (Metric)** 44.5 mm

### Logistics and Packaging

**Quantity Per** bag

**Package Quantity (Metric)** 1000 Pieces

**Carton Quantity** 5000

## Material and Specifications

---

<b>Material</b>	Polypropylene (PP)
<b>Material Shortcut</b>	PP
<b>Flammability</b>	UL94 HB
<b>Halogenfree</b>	Yes
<b>Operating Temperature</b>	-40°F to +239°F (-40°C to +115°C)
<b>ROHS Compliant</b>	Yes
<b>UL Listed (US and Canada)</b>	No
<b>UL Recognized (US and Canada)</b>	No