

Product information

71 31 160

KNIPEX CoBolt® S

Compact Bolt Cutters

With recess in the cutting edge



- Heavy-duty cutting edge with recess slices through the hardest round materials in only one cutting action
- Extremely high cutting performance in a convenient length of 160 mm
- Small, slim head for excellent accessibility
- Compact and powerful: cuts bolts, nails, rivets etc. up to Ø 4.8 mm
- Cutting edge hardness approx. 64 HRC
- Less physical effort due to efficient lever action mechanism
- Slippage of cutting material reduced by lasered cutting edge
- With gripping surface below the joint for gripping and pulling wires from Ø 1.0 mm
- Blades with recess for easier cutting of larger cross-sections thanks to better leverage close to the fulcrum
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



| General | |
|-----------------|--------------------|
| Article No. | 71 31 160 |
| EAN | 4003773084587 |
| Pliers | black atramentized |
| Handles | plastic coated |
| Weight | 200 g |
| Dimensions | 160 x 45 x 14 mm |
| REACH compliant | contains SVHC |
| RoHS compliant | not applicable |

| Technical details | |
|--|----------|
| Cutting capacities soft wire (diameter) | Ø 5.3 mm |
| Cutting capacities medium hard wire (diameter) | Ø 4.8 mm |
| Cutting capacities hard wire (diameter) | Ø 3.6 mm |
| Cutting capacities piano wire (diameter) | Ø 3.3 mm |

technical change and errors excepted



