DFCC1V

Fuse carrier TeSys DF, 1P 30A, fuse class CC, blown fuse indicator





Main	
Range	TeSys
Product name	TeSys DF
Product or component type	Fuse carrier
Device short name	DFCC
Poles description	1P
Fuse type	, CC
Control type	Toggle padlockable
Local signalling	Blown fuse indication
Utilisation category	AC-20B IEC 60947-3
[Ue] rated operational voltage	600 V AC
[le] rated operational current	30 A
[Ui] rated insulation voltage	600 V AC
[Uimp] rated impulse withstand voltage	6 kV
Short-circuit withstand	200 kA 600 V UL 512
Power dissipation in W	3 W maximum power dissipation by fuse

Complementary

Complementary	
Standards	UL 4248-1 UL 4248-4 CSA C22.2 No 4248-1 CSA C22.2 No 4248-4
Product certifications	UL Recognized CSA
Mounting support	35 mm symmetrical DIN rail
Mounting position	Vertical +/- 23°)
Connections - terminals	Screw clamp terminals 1 0.000.02 in² (116 mm²)rigid Screw clamp terminals 2 0.000.01 in² (16 mm²)rigid Screw clamp terminals 1 0.000.02 in² (116 mm²)flexible with or without Screw clamp terminals 2 0.000.01 in² (16 mm²)flexible with or without
Tightening torque	17.70 Lbf.In (2 N.m) PZ2 17.70 lbf.in (2 N.m) flat Ø 5.5 mm
Height	3.13 in (79.5 mm)
Maximum Width	0.69 in (17.5 mm)
Depth	2.40 in (61 mm)
Net Weight	0.09 lb(US) (0.042 kg)
Quantity per set	Set of 12

Environment

Ambient air temperature for storage	-4070 °C	
Ambient air temperature for operation	-40158 °F (-4070 °C) with derating above 20°C	
Operating altitude	02000 m without derating	
IP degree of protection	IP20	
Pollution degree	3	
Fire resistance	1760 °F (960 °C) IEC 60695-2-1	
Compatibility code	DFCC	

Ordering and shipping details

21714 - DF FUSEHOLDERS
CP1
00785901879145
12
0.13 lb(US) (0.06 kg)
Yes
FR

Packing Units

Package 1 Height	0.885 dm
Package 1 width	0.175 dm
Package 1 Length	0.645 dm

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov
REACh Regulation	☑ REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Compliant E EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	₫Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

	·
Warranty	18 months