



Art. no.	17673 788
Suitable for knife width	4 mm
Shaft diameter	40 mm
Programming size	12 mm
Length	300 mm
Clamping surface height	38.5 mm
Adjustment rate via centre	32.5 mm
Min. bore diameter	51.7 mm
Tool design	Left

EAN-Code

4050293740448