

## Spacer

for stainless steel jointed hose systems

**ORION**<sup>®</sup>

### Application:


For individual length and position adjustment of the jointed hose system.

### Execution:

- made from rust-free stainless steel (1.4301)
- suitable up to at least 40 bar operating pressure
- SW 11 and 16 width across flats on 6-mm system
- Clamping width 14 and 20 across flats on 8.8-mm system

### Advantage:

- extremely long service life, resistant to corrosion
- resistant to temperature and chemical substances
- fully rigid and individually adjustable thanks to screw coupling
- will not push away due to pressure, vibration or chips



<b>Art. no.</b>	<b>18300 470</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	18300470
<b>Type</b>	Spacer, 37 mm
<b>System design</b>	8.8 mm
<b>Gross Weight</b>	0.031 kg
<b>Product Group</b>	1FH

### EAN

4053625199228