

## Type ERICKSON collets

For ERICKSON system

**ORION**<sup>®</sup>

### Application:

For clamping tools with straight shank.

### Execution:

- For short chuck system ERICKSON sealing taper/sealing taper shank no. 23325.
- Multi-range collets for clamping the nominal diameter.
- Concentricity 20 µm.
- Clamp bridge -0.5 mm.

### Delivery:

1x type ERICKSON collet.



<b>Art. no.</b>	<b>23326 022</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	23326022
<b>Type</b>	416E
<b>Collet type</b>	DKS
<b>Clamping diameter</b>	1.5 mm
<b>Min./max. clamping range</b>	1-4 mm
<b>Gross Weight</b>	0.042 kg
<b>Product Group</b>	218

### EAN

4039247157174