

## Hydraulic pressure cylinder RSM (flat)



### Execution:

- Single-acting cylinder.
- Extra flat.
- With spring return and scraper ring
- Operating pressure of 700 bar.
- Bronzed piston rod.

### Advantage:

- Retaining ring prevents piston rod from being pushed out.

### Delivery:

1x ENERPAC hydraulic pressure cylinder RSM 50.



<b>Art. no.</b>	<b>29521 030</b>
<b>Brand</b>	ENERPAC
<b>Manufacturer Part Number</b>	RSM300
<b>Model</b>	RSM 300
<b>Max. compressive force</b>	295 kN
<b>Lift height</b>	13 mm
<b>Oil capacity</b>	55 cm <sup>3</sup>
<b>Construction height, retracted</b>	58 mm
<b>Housing outer diameter</b>	117 mm
<b>Diameter of hydraulic piston</b>	95 mm
<b>Weight</b>	4.5 kg
<b>Gross Weight</b>	4.715 kg
<b>Product Group</b>	258