

## Electronic pocket vernier callipers

IP67

**ORION**<sup>®</sup>

### Application:

For measuring external, internal, step and depth dimensions.

### Execution:

- ON/OFF
- Zero setting at any position
- mm/inch switch-over

### Advantage:

- Depth gauge: flat design with narrow probe tip, length 22 mm, for depth measurements in small boreholes from 2.5 mm diameter

### Delivery:

In a case, with battery (1 x 3 V lithium type CR 2032)



<b>Art. no.</b>	<b>31177 115</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	31177115
<b>Min./max. length measuring range</b>	0-150 mm
<b>Depth gauge rod</b>	Flat
<b>IP protection class</b>	IP 67
<b>Length of jaw</b>	40 mm
<b>Length of cross tips</b>	16 mm
<b>Digit increment</b>	0.01 mm
<b>Digit increment in inches</b>	0.0005 in
<b>Type of locating</b>	With locking screw
<b>With automatic shut off</b>	No
<b>Battery designation</b>	3V CR2032 Lithium
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Weight of rechargeable battery/battery</b>	0.003 kg
<b>Battery voltage</b>	3 V
<b>Type of rechargeable battery/battery</b>	Lithium
<b>Calibration Group</b>	A
<b>ISO</b>	13385-1
<b>Gross Weight</b>	0.300 kg
<b>Product Group</b>	3BH

### EAN

4053625306206