



M8 FEMALE FLANGE PLUG REAR MOUNT

TPE wires 3x0.25 0.2m

Rear mounting
Mounting nut
Flange M8 female
with multi-strand wire
3-pole

[Link to Product](#)**Illustration**

Female



Product may differ from Image

Form

08575

Technical Data

Operating voltage	max. 60 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M8 × 1 mm (recommended torque 0.4 Nm) self-securing
Protection	IP67 inserted and tightened (EN 60529)

Cables

Cable number	970
No./diameter of wires	3 × 0.25 mm ²
Wire isolation	PP (br, bk, bl)
Shore hardness outer jacket	70 ± 5D
Outer diameter	approx. 1.25 mm
Bend radius (fixed)	5 × outer Ø
Bend radius (moving)	10 × outer Ø
Temperature range (fixed)	-40...+80 °C
Temperature range (mobile)	-25...+80 °C

General data

The information in this brochure has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 05/15

Temperature range -25...+85 °C

Commercial data

country of origin DE

customs tariff number 85444290

minimum order quantity 1