

## Product information

# 68 01 160

## End Cutting Nipper

DIN ISO 5748

- The head shape provides optimised movement when tightening steel mesh knots during reinforced concrete work
- With cutting edges for soft and hard wire
- Also suitable for twisting and cutting binding wire
- Cutting edges additionally hardened; cutting edge hardness approx. 61 HRC
- High-grade special tool steel, forged, multi stage oil-hardened



### General

Article No.	68 01 160
EAN	4003773013792
Pliers	black atramentized
Head	polished
Handles	plastic coated
Weight	202 g
Dimensions	160 x 53 x 14 mm
Standard	DIN ISO 5748
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Cutting capacities soft wire (diameter)	Ø 4.0 mm
Cutting capacities medium hard wire (diameter)	Ø 2.8 mm
Cutting capacities hard wire (diameter)	Ø 2.3 mm
Cutting edge length mm (C)	25 mm

*technical change and errors excepted*

