

Product information


97 52 34

KNIPEX PreciForce® Crimping Pliers

- Consistently high crimping quality thanks to precision dies and ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Special quality chrome vanadium electric steel, oil-hardened



General	
Article No.	97 52 34
EAN	4003773051879
Pliers	burnished
Handles	with multi-component grips
Weight	483 g
Dimensions	220 x 59 x 21 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details	
	
Application	non-insulated open plug type connectors (plug width 2.8 + 4.8 mm)
Capacity in square millimetres	0.1 — 2.5 mm ²
Number of crimping positions	4
AWG	27 — 13

technical change and errors excepted