

Temperature & Humidity Sensors

The Tempatron DP series temperature and humidity sensors are designed for sensing temperature and humidity in commercial and industrial applications. Temperature only versions are available as well as combined temperature and humidity versions.

The sensors are available in wall mounting, duct mounting and industrial environment wall mounting enclosures and have a selectable 0-1Vdc or 4-20mA output.

These high accuracy sensors have an enclosure code of up to IP55 and are powered from a 8 to 30Vdc or 12-24Vac.

Models Available

DPWT Wall Mounting Temperature Sensor **DPWC** Wall Mounting Temperature &

Humidity Sensor

DPDT Duct Mounting Temperature Sensor

DPDC Duct Mounting Temperature & Humidity Sensor

DPPT Industrial Environment Temperature
Sensor

DPPC Industrial Environment Temperature & Humidity Sensor

Product Features


- Temperature range from -20 to +70°C
- Humidity range from 0-100% rH
- Selectable 0-1V or 4-20mA output
- 8 to 30Vdc or 12 to 24Vac powered
- Duct or industrial sensors IP55
- Wall sensors IP30

Temperature & humidity sensors for commercial and industrial applications

Connections


DPD DUCT MOUNTING DPD DUCT MOUNTING DPD DUCT MOUNTING

DPP INDUSTRIAL WALL MOUNTING




CVRLL

All dimensions in mm



DPxxxx1xxx



Ordering information

Model	Code	Description
	DPW	Wall Mounting Sensor
	DPD	Duct Mounting Sensor
	DPP	Industrial Environment Wall Mounting Sensor
Input	Code	Description
	Т	Temperature Only
	С	Temperature and Humidity
Humidity Input	Code	Description
	0	N/A
	1	10-90% rH
	2	0-100% rH
Temperature Input	Code	Description
	0	N/A
	1	NTC
Output	Code	Description
	0000	0-1Vdc or 4-20mA
	1000	0-1Vdc or 4-20mA & NTC Resistive Output
 Example	DPDC111000	

Specification

Power Supply Voltage:

- 8 to 30Vdc (±15%)
- 12 to 24Vac (-10/+15%)

Frequency:

- 50/60Hz

Temperature Accuracy:

- NTC:
 - ±0.25% at 25°C, ±1.2% 0 to 50°C
- 0 to 50°C:
- ±0.4% at 25°C, ±1.2% 0 to 50°C
- -10 to 70°C:
 - ±0.2% at 25°C, ±0.7% -10 to 70°C

Humidity Accuracy:

- 10-90%rH:
 - ±3% at 25°C, ±6% 0 to 50°C
- 0-100%rH:
- ±3% at 25°C, ±5% -10 to 70°C

Temperature Output:

10mV/°C or 4-20mA

Humidity Output:

- 10mV/%rH or 4-20mA

Operating Range:

- DPWT: -10 to 60°C
- DPWC: -10 to 60°C, 10-90% rH
- DPDT/DPPT: -20 to 70°C
- DPDC/DPPC: -20 to 70°C, 10-90% rH

Storage Temperature:

- -20°C to 70°C
- 10-90% rH (non-condensing)

Enclosure Code:

- DPW: IP30
- DPD: IP55
- DPP: IP55

Weight:

- DPW: 200g
- DPD: 450g
- DPP: 300g

Markings:

 CE marked (meets EN61010-1 low voltage and EN50081-1/50082-1 EMC directives)

Specification subject to change without notice.

Tempatron: Eltime House, Hall Road, Maldon, Essex, CM9 4NF UK.

