

Micro-abrasive IBE pipe brushes with sanding bristles

For use on electronic drills

LESSMANN®

Application:

Particularly suitable for deburring bores, horizontal bore holes or O-ring inserts in complex workpieces, as well as for polishing and cleaning nozzles and small holes.



Execution:

- Internal cleaning brushes with galvanised twisted wire and a basic spiral of bristles: - Aluminium oxide (AO) sanding bristles: for finishing soft metals, for polishing and smoothing and for processing of aluminium while smoothing or polishing. - Sanding bristles made of silicon carbide (SiC): for optimum deburring results, for surface repair/processing and especially for processing aluminium and stainless steel.
- Aluminium oxide (AO) sanding bristles are suitable for finishing soft metals, for polishing and smoothing, and for processing aluminium during smoothing or polishing.
- Sanding bristles made of silicon carbide (SiC) are suitable for optimum deburring results, for surface repair/processing and especially for processing aluminium and stainless steel

Advantage:

- Can be used flexibly as a conventional internal cleaning brush due to sanding bristles

Art. no.	76099 025
Brand	LESSMANN
Manufacturer Part Number	541076
Grid size	AO 600
Wire diameter	0.3 mm
Head diameter	8.2 mm
Length	125 mm
Length of bristles	25 mm
Shank diameter	3.2 mm
Max. rotation speed	2000 rpm
Number of pieces per packet	10 PCS
Gross Weight	0.007 kg
Product Group	6CL

EAN

4017359154939