

**Cable glands
VP M40-MS65**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



For sealing surplus threaded holes to maintain the IP class of protection

General ordering data

Type	VP M40-MS65
Order No.	177770000
Version	Cable glands, Blanking plug, Brass, nickel-plated, M 40, IP 68
GTIN (EAN)	4032248158041
Qty.	50 pc(s).

**Cable glands
VP M40-MS65**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	13 mm	Net weight	41.9 g
--------	-------	------------	--------

General information

Cable gland	metric	External thread	M 40
Head diameter	44 mm	Length of thread	8 mm
Material	Brass, nickel-plated	O-Ring	NBR
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.5 mm	Sealing	NBR

Classifications

ETIM 3.0	EC000032	UNSPSC	30-21-18-01
eClass 5.1	27-14-91-10	eClass 6.2	27-14-91-10
eClass 7.1	27-14-91-10		

Product information

Descriptive text ordering data Other versions available on request. The sealing plugs must be tightened "hand-tight" with the screwdriver.

Approvals

Approvals



ROHS Conform