




TAGPU LOOP

Flexible identification without cable ties

MADE FOR REAL 



Identification tags for cable bundle, "Ladder Style", thermal transfer

TAGPU – UV-stabilised Tiptags

TAGPU LOOP is a specially designed cable marker for identifying wires and cables without using a cable tie. The markers are looped on cables and wires from 2.8 mm to 35 mm, where a permanently legible and UV resistant marking is required. The cable markers consist of a robust and flexible polyurethane material and are especially suited for harsh environments. The material has been conditioned for printing on both thermal transfer and laser beam printers. Simply print and press out the required TAGPU and apply with cable ties.

Print with HellermannTyton's premium range of thermal printers and ribbons or a laser beam marking device.


Features and benefits

- Using without cable ties - Cost and time savings
- UV-stabilised
- Robust and flexible material
- Thermal transfer or laser beam printable
- Available in various colours
- Halogen Free
- Good mechanical strength and highly flexible
- Delivery in convenient storage boxes




TAGPU LOOP - Cable marking solutions for labeling on the inverter.

| | |
|---------------------------------|--------------------|
| MATERIAL | Polyurethane (PUR) |
| Operating Temperature | -25 °C to +105 °C |
| Flammability | UL 94 V0 (3 mm) |
| Recommended Ribbon Type | TTRHT, TTRC+ |
| Thermal Transfer Printer | TT431, TT4030 |



TAGPU12X74



TAGPU18X124

| TYPE | Length (L) | Length (L2) | Width (W) | Bundle Ø min. | Bundle Ø max. | Pack Cont. | Colour | Article-No. |
|-----------------|------------|-------------|-----------|---------------|---------------|------------|-------------|-------------|
| TAGPU12X74-LOOP | 74.0 | 40.0 | 12.0 | 2.8 | 8.0 | 500 pcs. | Blue (BU) | 556-80586 |
| | 74.0 | 40.0 | 12.0 | 2.8 | 8.0 | 500 pcs. | Red (RD) | 556-80587 |
| | 74.0 | 40.0 | 12.0 | 2.8 | 8.0 | 500 pcs. | White (WH) | 556-80584 |
| | 74.0 | 40.0 | 12.0 | 2.8 | 8.0 | 500 pcs. | Yellow (YE) | 556-80585 |

All dimensions in mm. Subject to technical changes. Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available. More colours on request.

| TYPE | Length (L) | Length (L2) | Width (W) | Bundle Ø min. | Bundle Ø max. | Pack Cont. | Colour | Article-No. |
|------------------|------------|-------------|-----------|---------------|---------------|------------|-------------|-------------|
| TAGPU18X124-LOOP | 124.0 | 40.0 | 18.0 | 4.0 | 35.0 | 300 pcs. | White (WH) | 556-80588 |
| | 124.0 | 40.0 | 18.0 | 4.0 | 35.0 | 300 pcs. | Yellow (YE) | 556-80589 |

All dimensions in mm. Subject to technical changes. Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available. More colours on request.