



Datasheet for part number DAMAY26P

Our Catalog Part Number: DAMAY-26P
Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*MA

Product Datasheet	
General	D*M High reliable D-Sub Connectors with crimp termination
Wire Gauge Range AWG	Standard: AWG 20-28. High Density: AWG 22-28
Mating Cycles	200
Contact Arrangement	Standard: 26 contacts size 20. High Density: 26 contacts size 22
Dielectric Withstanding Voltage	1000 VAC at sea level
Current Rating	7.5 A max
Contact Resistance	10 milli Ohm max
Operating Temperature	-55°/+125°
Salt Spray Test	24 hours
Shell Material	steel
Shell Finish	Yellow chromate over zinc
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Gender	Pin
Contact Type	Crimp
Contact Material	copper alloy
Contact Finish	gold over nickel
Hardware	Dual Float Mount