




-20°C OVERSIZE PAINTED VERTICAL AIR VESSELS



DIRECTIVE 2014/68/UE (PED)

OPERATING PRESSURE 8/12/16 BAR

OPERATING TEMPERATURE -20 +80°C

- MATERIAL: CARBON STEEL
- FLUID CONTENT: COMPRESSED AIR / NITROGEN / ARGON / HELIUM / OIL / OXYGEN (GROUP 1 - HYDROGEN AND WATER EXCLUDED)
- FINISHING: EXTERNAL RAL 5015 BLUE PAINT (STANDARD)
- UPON REQUEST: INSPECTION PORTS - 100x150 mm HANDHOLE - 300x400 mm MANHOLE

Directive	Capacity	Operating Pressure	De	A	B	C	D	E	F	L	1	2-3-4-5	6-7-8-9	10	11	Weight
RAL 5015	Lt	Bar	mm	mm	mm	mm	mm	inch	inch	inch	inch	inch	inch	inch	inch	Kg
2014/68/UE (PED)	5000	8	1650	175	1150	2200	=	=	1950	3200	2"	3"	=	3/4"	3/8"	1120
2014/68/UE (PED)	8000	8	1650	175	1150	1930	2460	3310	1680	4315	2"	3"	3"	3/4"	3/8"	1400
2014/68/UE (PED)	10000	8	1650	175	1150	2200	3150	4250	1950	5200	2"	3"	3"	3/4"	3/8"	1730
2014/68/UE (PED)	4000	12	1450	225	800	2145	=	=	=	2790	2"	3"	=	3/4"	3/8"	835
2014/68/UE (PED)	5000	12	1450	225	800	2745	=	=	=	3390	2"	3"	=	3/4"	3/8"	962
2014/68/UE (PED)	5000	12	1650	175	1150	2200	=	=	1950	3200	2"	3"	=	3/4"	3/8"	1360
2014/68/UE (PED)	6000	12	1450	225	800	3345	=	=	=	3990	2"	3"	=	3/4"	3/8"	1090
2014/68/UE (PED)	8000	12	1650	175	1150	1930	2460	3310	1680	4315	2"	3"	3"	3/4"	3/8"	1730
2014/68/UE (PED)	10000	12	1650	175	1150	2200	3150	4250	1950	5200	2"	3"	3"	3/4"	3/8"	2015
2014/68/UE (PED)	4000	16	1450	225	800	2145	=	=	=	2790	2"	3"	=	3/4"	3/8"	995
2014/68/UE (PED)	5000	16	1450	225	800	2745	=	=	=	3390	2"	3"	=	3/4"	3/8"	1145
2014/68/UE (PED)	6000	16	1450	225	800	3345	=	=	=	3990	2"	3"	=	3/4"	3/8"	1295
2014/68/UE (PED)	10000	16	1650	175	1150	2200	3150	4250	1950	5200	2"	3"	3"	3/4"	3/8"	2585