



MEHRBEREICHSBLINDNIETE SENKKOPF 120°

MULTIGRIP BLIND RIVETS COUNTERSUNK HEAD 120°


RIVETS MULTI SERRAGE TÊTE FRAISÉE 120°









Aluminium AIMG 2,5
Aluminium AIMG 2,5
Aluminium AIMG 2,5


Edelstahl A2 [1.4301]
Stainless steel A2 [AISI 304]
Acier inox A2 [1.4301]







Ø 4,0 mm

D1 = 4,0 + 0,05 / - 0,13 mm
D2 = 8,0 + 0 / - 0,29 mm
k = -
d = 2,18 mm
P = ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 4,1 mm

	F-Max		CODE				
4,0 x 9,5 mm	13,5 mm	2,0 - 6,0 mm	77744 40950	1050 N	1300 N	1000	10000
4,0 x 12,5 mm	16,5 mm	4,0 - 9,0 mm	77744 40125			1000	10000
4,0 x 17,0 mm	21,0 mm	8,5 - 13,5 mm	77744 40170			500	5000

Ø 4,8 mm

D1 = 4,8 + 0,05 / - 0,13 mm
D2 = 9,5 + 0 / - 0,29 mm
k = -
d = 2,78 mm
P = ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 4,9 mm

	F-Max		CODE				
4,8 x 12,0 mm	16,5 mm	2,0 - 8,0 mm	77744 48120	1400 N	2000 N	500	5000
4,8 x 16,9 mm	21,4 mm	6,4 - 12,7 mm	77744 48169			500	5000
4,8 x 20,0 mm	24,5 mm	10,0 - 15,0 mm	77744 48200			500	5000