

- Manual Pull Down Screens
- Wall/Ceiling Manual Pull Down Front Projection Screen

Manual Series



Electric Screens


Features and Benefits

- Dual Wall and ceiling Installation Design
- Auto Locking System provides variable height settings
- Standard 4-side Black Masking Borders
- MaxWhite™ Screen Material is durable and easy to clean
- 160 Degrees Wide Viewing Angle for commercial Presentation or Residential Home Cinema
- Available with Black or White casings
- Screen Lanyard for easy operation included
- Black Backed Screen material eliminates light penetration for superior color reproduction
- In-Stock available from 71" (180 cm) - 170" (431.8 cm) in 1:1, 4:3, 16:9 & 16:10 Aspect Ratio
- Two Year Manufacturer's Warranty
- Optional 6" - 18 Hanging Brackets Available

Fixed Frame Screens



Portable Screens



Elite Screens' MaxWhite™ Screen Material is durable for daily use and Easy to Clean. It has a wide viewing angle with 1.1 Gain and is suitable for most applications including commercial/Educational and Residential. MaxWhite™ Screen material has a black backing to eliminate light penetration for superior color reproduction. Its Texture pattern eliminates Moiré or Hot Spotting which is a common phenomenon with poorly made projection screen material or wall projections.



Optional 6", 12" or 18" Brackets can always provide more flexibility with an installation. Please contact your reseller or visit shop.elitescreens.com for accessory parts.



Available in Black and White Casing Colors.



Lanyard Included for Convenient Operation



Black-Backed Screen Material

Elite Screens stocks all sizes from 71" to 170" in 1:1, 4:3, 16:9 and 16:10 aspect ratios. Choose from white or black metallic casing options.

Manual Series: Business/Education Manual (1:1) Pull Down Projector Screen

Model	Nominal Diagonal	View Height (in)	View Width (in)	View Height (cm)	View Width (cm)	Ship via UPS or FedEx	Net Weight (lbs)	Net Weight (kg)	Gain	Screen Material	Case Color	Top Black Masking Border
M71UWS1	71" (1:1)	50.0	50.0	127.0	127.0	Yes	10.1	4.6	1.1	MaxWhite	Black	1.5" (3.8cm)
M71XWS1	71" (1:1)	50.0	50.0	127.0	127.0	Yes	10.1	4.6	1.1	MaxWhite	White	1.5" (3.8cm)
M85UWS1	85" (1:1)	60.0	60.0	152.4	152.4	Yes	12.6	5.7	1.1	MaxWhite	Black	1.5" (3.8cm)
M85XWS1	85" (1:1)	60.0	60.0	152.4	152.4	Yes	12.6	5.7	1.1	MaxWhite	White	1.5" (3.8cm)
M99NWS1	99" (1:1)	70.0	70.0	177.8	177.8	Yes	16.7	7.6	1.1	MaxWhite	White	1.5" (3.8cm)
M99UWS1	99" (1:1)	70.0	70.0	177.8	177.8	Yes	16.7	7.6	1.1	MaxWhite	Black	1.5" (3.8cm)
M113NWS1	113" (1:1)	80.0	80.0	203.2	203.2	Yes	19.3	8.8	1.1	MaxWhite	White	1.5" (3.8cm)
M113UWS1	113" (1:1)	80.0	80.0	203.2	203.2	Yes	19.3	8.8	1.1	MaxWhite	Black	1.5" (3.8cm)
M119UWS1	119" (1:1)	84.0	84.0	213.4	213.4	Yes	20.9	9.5	1.1	MaxWhite	Black	1.5" (3.8cm)
M119XWS1	119" (1:1)	84.0	84.0	213.4	213.4	Yes	20.9	9.5	1.1	MaxWhite	White	1.5" (3.8cm)
M136UWS1	136" (1:1)	96.0	96.0	243.8	243.8	Yes	23.9	10.8	1.1	MaxWhite	Black	4" (10cm)
M136XWS1	136" (1:1)	96.0	96.0	243.8	243.8	Yes	23.9	10.8	1.1	MaxWhite	White	4" (10cm)
M170XWS1	170" (1:1)	120.0	120.0	304.8	304.8	No	35.7	16.2	1.1	MaxWhite	White	4" (10cm)

Manual Series: Home Cinema (4:3 and 16:9) Manual Pull Down Projector Screen

Model	Nominal Diagonal	View Height (in)	View Width (in)	View Height (cm)	View Width (cm)	Ship via UPS or FedEx	Net Weight (lbs)	Net Weight (kg)	Gain	Screen Material	Case Color	Top Black Masking Border
M80NWX	80" (4:3)	48.0	64.0	121.9	162.6	Yes	12.7	5.8	1.1	MaxWhite	White	1.5" (3.8cm)
M84NWX	84" (4:3)	50.3	67.0	127.8	170.2	Yes	13.7	6.2	1.1	MaxWhite	White	1.5" (3.8cm)
M100NWX1	100" (4:3)	60.0	80.0	152.4	203.2	Yes	18.0	8.2	1.1	MaxWhite	White	3" (7.6cm)
M100UWX1	100" (4:3)	60.0	80.0	152.4	203.2	Yes	18.0	8.2	1.1	MaxWhite	Black	1.5" (3.8cm)
M120UWX2	120" (4:3)	72.0	96.0	182.9	243.8	Yes	22.0	10.0	1.1	MaxWhite	Black	2" (5cm)
M120XWX2	120" (4:3)	72.0	96.0	182.9	243.8	Yes	22.0	10.0	1.1	MaxWhite	White	2" (5cm)
M135UWX2	135" (4:3)	81.0	108.0	205.7	274.3	No	31.2	14.2	1.1	MaxWhite	Black	1.5" (3.8cm)
M135XWX2	135" (4:3)	81.0	108.0	205.7	274.3	No	31.2	14.2	1.1	MaxWhite	White	1.5" (3.8cm)
M150UWX2	150" (4:3)	90.0	120.0	228.6	304.8	No	35.3	16.0	1.1	MaxWhite	Black	4" (10.2cm)
M150XWX2	150" (4:3)	90.0	120.0	228.6	304.8	No	35.3	16.0	1.1	MaxWhite	White	4" (10.2cm)
M84UWH	84" (16:9)	41.0	73.0	104.1	185.4	Yes	13.7	6.2	1.1	MaxWhite	Black	1.5" (3.8cm)
M84UWH-E30	84" (16:9)	41.0	73.0	104.1	185.4	Yes	13.7	6.2	1.1	MaxWhite	Black	30" (76.2cm)
M84XWH-E30	84" (16:9)	41.0	73.0	104.1	185.4	Yes	13.7	6.2	1.1	MaxWhite	White	30" (76.2cm)
M92UWH	92" (16:9)	45.1	80.2	114.6	203.7	Yes	15.6	7.1	1.1	MaxWhite	Black	3" (7.6cm)
M100UWH	100" (16:9)	49.0	87.0	124.5	221.0	Yes	20.1	9.1	1.1	MaxWhite	Black	3" (7.6cm)
M100XWH	100" (16:9)	49.0	87.0	124.5	221.0	Yes	20.1	9.1	1.1	MaxWhite	White	3" (7.6cm)
M100XWH-E24	100" (16:9)	49.1	87.2	124.7	221.5	Yes	20.1	9.1	1.1	MaxWhite	White	24" (61cm)
M106UWH	106" (16:9)	52.0	92.4	132.1	234.7	Yes	20.7	9.4	1.1	MaxWhite	Black	4" (10.2cm)
M120UWH2	120" (16:9)	58.8	104.6	149.4	265.7	No	23.4	10.6	1.1	MaxWhite	Black	3" (7.6cm)
M120XWH2	120" (16:9)	58.8	104.6	149.4	265.7	No	23.4	10.6	1.1	MaxWhite	White	3" (7.6cm)
M120XWH2-E24	120" (16:9)	58.5	104.0	148.6	264.2	No	23.4	10.6	1.1	MaxWhite	White	24" (61cm)
M135UWH2	135" (16:9)	66.0	117.3	167.6	298.0	No	31.1	14.1	1.1	MaxWhite	Black	1.5" (3.8cm)
M135XWH2	135" (16:9)	66.2	117.7	168.1	299.0	No	31.1	14.1	1.1	MaxWhite	White	1.5" (3.8cm)
M150UWH2	150" (16:9)	73.5	130.7	186.7	332.0	No	35.9	16.3	1.1	MaxWhite	Black	1.5" (3.8cm)
M150XWH2	150" (16:9)	73.5	130.7	186.7	332.0	No	35.9	16.3	1.1	MaxWhite	White	4" (10.2cm)

Manual Series: Business/Education Manual Pull Down Projector Screen (16:10)

Model	Nominal Diagonal	View Height (in)	View Width (in)	View Height (cm)	View Width (cm)	Ship via UPS or FedEx	Net Weight (lbs)	Net Weight (kg)	Gain	Screen Material	Case Color	Top Black Masking Border
M94UWX	94" (16:10)	49.8	79.7	126.5	202.4	Yes	18.5	8.4	1.1	MaxWhite	Black	4" (7.6cm)
M128UWX	128" (16:10)	67.8	108.4	172.2	275.3	No	30.0	13.6	1.1	MaxWhite	Black	4" (7.6cm)