

INTRODUCTION

Remind: Please note that this item doesn't include **AG13 button cell** since it cannot be shipped, so our warehouse will ship the thermometer **without battery**. Make sure you can buy the battery separately before purchasing. Thanks for your understanding.

Are you still looking for a low-cost thermometer? Did you get one? Aha! Here it is! This is a new waterproof digital thermometer with display. It is suitable for greenhouse, fish tank, swimming pool and other application scenarios which require temperature measurement. It is completely waterproof to a depth of one meter for long time. And it can continuously work for half the year with only 2 AG13 button cell.



Application:

- Vehicle temperature measurement
- Indoor temperature measurement
- Fridge temperature measurement
- Body temperature measurement
- Fish Tank/ Swimming Pool temperature measurement

SPECIFICATION

- Temperature Measurement Range: - 50℃ ~ 110℃
- Temperature Measurement Error: ±1℃

- Resolution: 0.1℃
- Refresh Rate: 1.5 ~ 2 seconds
- Operating Voltage: 2x AG13 button cells
- Operating current: 4 uA (Max)
- Probe Cable Length: 1 m
- probe length: 20 mm (1 meters waterproof probe)
- Operating Temperature: 0℃ ~ 50℃
- Storage temperature: - 10℃ ~ 60℃
- Dimension: 4.8 * 2.8 * 1.5 cm/ 1.89 * 1.1 * 0.59 inches
- Weight: 28g

SHIPPING LIST

- Digital Thermometer x1 (**without battery AG13 button cell x2**)