

Grid vacuum plate sets

With Venturi nozzle for dry machining

ATORN®

Application

For simple geometric workpieces with rough shapes without breakouts or large breakouts that can be sealed with sealing cords (size must be a multiple of the grid).

Version


- With Venturi nozzle
- All grid vacuum plates can also be connected to conventional vacuum pump no. 24501 110 or no. 24501 120.
- Operating pressure approx. 6 bar
- Depending on conditions of use, end vacuum up to 92%, air consumption approx. 95 l/min.

Advantage

- Minor unevenness and curvatures are sealed and compensated for with the elastic sealing cords.
- Good sealing, also suitable for rough (e.g. sawn) surfaces
- High retention forces, especially suitable for heavy machining such as milling and grinding

Delivery

1 matching vacuum grid plate with a grid pattern of 12.5 mm, including built-in compressed air vacuum ejector. Mounting grooves and height-adjustable stop discs, 4 x adjustable clamp with a groove width of 14 mm, 1 plastic hose connection for 3 m quick-release coupling, black vacuum sealing cord with 4 mm diameter, 10 m, 1 vacuum generator including silencer and shut-off valve, 1 connection for conventional vacuum pump.



Art. No.	24504 020
Model	RV 2
Vacuum panel length	400 mm
Vacuum panel height	32.5 mm
Vacuum panel width	300 mm
Grid dimension	12.5 mm
Vacuum panels, can be linked	No

EAN-Code

4050293354003