

Electronic depth callipers

Lightweight design incl. 3 measuring bridges

ORION[®]

Application:

For measuring, e. g. hole depths, distances on workpieces etc.

Execution:

- ON/OFF
- Zero setting at any position
- mm/inch switch-over
- Measuring bridges 150/300/450 mm

Advantage:

- Internal double vee-block guide for optimum guidance and slide properties
- Replaceable blade tips M2.5

Delivery:

In a case, gauge slide with ball, with battery (1 x type SR 44, 1.55 V)



Art. no.	31115 208
Brand	ORION
Manufacturer Part Number	31115208
Min./max. length measuring range	0-800 mm
Digit increment	0.01 mm
Error limit	0.06 mm
IP protection class	IP 40
Bridge length x bridge width	150 x 13 mm
Type of locating	With locking screw
Calibration Group	B
Number of rechargeable batteries/batteries	2 PCS
Display	Digital
Battery designation	LR44
ISO	13385-2
Bridge length	150 mm
Gross Weight	4.300 kg
Product Group	3BI

EAN

4053625204885