

ESD shelf trolley 9000 series, load capacity 300 kg

In 4 sizes and with 2, 3 and 4 load areas



Application:

Ideal as a transport and picking trolley for many types of goods, including sensitive electrical equipment.

Execution:

- Electrolytically galvanised, highly stable tubular frame structure with front and rear grid
- Electrically conductive load areas, SP tested and heat-resistant up to 400°C

Advantage:

- Continuously height-adjustable load areas
- Ergonomic - height-adjustable push handle
- Helps to transport goods more efficiently



Art. no.	50290 007
Brand	KONGAMEK
Manufacturer Part Number	KM9000-2M-ESDB
Load-carrying capacity	300 kg
Load-carrying capacity of loading surfaces	100 kg
Colour	Silver coloured
Material of loading surface	Wood, electroconductive
Number of loading surfaces	2
Loading surface length	1390 mm
ESD-capable	Yes
Loading-surface width	650 mm
Length	1390 mm
Width	650 mm
Height	1025 mm
Loading surface size	1390 x 650 mm
Surface	Zinc plated
Length x width x height	1390 x 650 x 1025 mm
With wheel lock	Yes
Wheel diameter	160 mm
Material of wheel	Solid rubber
Number of steering rollers	4
Made in	Sweden
Gross Weight	39.000 kg
Product Group	5AT

EAN

7350112290640