

Jointed hose module

For MAXIFLEX® jointed hose systems



Application:

For adjusting the length and position of the jointed hose system.

Execution:

- Made from high-quality and robust plastic
- 1/4" version with 6.35 mm internal diameter
- 1/2" version with 12.7 mm internal diameter
- Max. 6 bar operating pressure

Advantage:

- Coolant is supplied precisely where it is needed.
- Resistant to chemicals and solvents
- Not electrically conductive
- Can be shortened or extended as desired



Art. no.	56495 220
Brand	WIHA
Manufacturer Part Number	27111
System design	1/2 inch
Type	Jointed hose module, overall length 265 mm
Outlet diameter	12.7 mm
Included in delivery	12 units
Gross Weight	0.082 kg
Product Group	575

EAN

4010995271114