



datasheet for KLEPS 250  
 article number: 973528101



<b>product description:</b>	<b>order number: 973 528-101</b>
<b>description:</b>	Contact-protected clamp-type test probe with rotating grip jaws and flexible shaft. The grip jaws allows clamping of pins and wires up to a max. of 4 mm diameter. Brass 4 mm diameter contact-protected socket connection. Connects with MLN and MLB measuring leads.
<b>typ:</b>	KLEPS 250 rot/red
<b>system:</b>	4mm sliding sleeve system
<b>order number:</b>	973 528-101
<b>clamping range:</b>	4 mm
<b>clamping typ:</b>	rotating grip jaws
<b>color</b>	
<b>other color versions:</b>	
<b>technical data</b>	
<b>measurement category acc. to IEC 61010:</b>	CAT I
<b>norm</b>	IEC 61010
<b>type of termination:</b>	4 mm socket (unsprung)
<b>rated voltage:</b>	30 VAC / 60 VDC
<b>rated current:</b>	4 A
<a href="#">Please consider derating curve!</a>	
<b>contact resistance:</b>	100 mOhm
<b>material</b>	
<b>contact material:</b>	grip jaws: spring steel socket: brass
<b>contact surface material:</b>	grip jaws: tin
<b>housing material:</b>	PF
<b>environmental conditions:</b>	
<b>temperature range:</b>	-25 °C to +80 °C
<b>inflammable class:</b>	
<b>housing (basic material):</b>	UL 94 V - 0
<b>drawing</b>	

