



# Full Moon

FULL MOON EM TUTTOSCH 18W 4K

Order code **75339**

EAN **8002219866714**

## Technical specifications

Absorbed Power	<b>18 W</b>
Supply voltage type	<b>AC</b>
Nominal voltage (AC)	<b>230 Vac</b>
Autonomy	<b>1.5h</b>
Battery included	<b>Yes</b>
Battery type	<b>Lithium-ions</b>
Battery	<b>Li-ion 3.6V 1.8Ah</b>
Ambient temperature (min)	<b>0 °C</b>
Ambient temperature (max)	<b>40 °C</b>
Insulation class	<b>II</b>
CCT light tone	<b>4000 K</b>
Photobiological risk	<b>RG0</b>
CRI color rendering	<b>&gt;80</b>
Diameter	<b>328 mm</b>
Efficiency	<b>80 lm/W</b>
Flux SE	<b>50 lm</b>
Frequency (max)	<b>60 Hz</b>
Frequency (min)	<b>50 Hz</b>
Power factor	<b>0.5</b>
Glow wire strength	<b>650 °C - 30s.</b>
Luminaire flux	<b>1440 lm</b>
Number of Batteries	<b>1</b>
Voltage supply range (max)	<b>265 V</b>
Voltage supply range (min)	<b>180 V</b>

## Mechanical specifications

Height	<b>77 mm</b>
Weight	<b>0.57 Kg</b>
Protection grade IP	<b>IP44</b>
Protection grade IK	<b>IK03</b>

## Certifications and norms

UK SI 2021 No. 1095, EN IEC 55015:2019 + A11:2020, EN IEC 61000-3-2 :2019, EN 61547:2009, EN 62471:2008, EN IEC 60598-1:2021, EN 60598-2-22:2014 + AC:2015 + AC:2016-05 + AC:2016-09 + A1:2020, EN IEC 63000:2018, EN 62493:2010, EN 61000-3-3:2013

