


E21152



Fibre optic diffuse reflection sensor

FT-00-M-W-M6/1,2M



Application

Function principle	Diffuse reflection sensor
--------------------	---------------------------

Detection zone

Range with fibre optic amplifier type	OKF
---------------------------------------	-----

OKF

Range fibre optics	[mm]	30
--------------------	------	----

Operating conditions

Ambient temperature	[°C]	-40...150
---------------------	------	-----------

E21152



Fibre optic diffuse reflection sensor

FT-00-M-W-M6/1,2M

Mechanical data		
Weight	[g]	85.5
Version of sensing head		straight
Sensing head thread		M6
Sensing head length	[mm]	35
Total length	[mm]	1200
Min. bending radius	[mm]	45
Fibre arrangement		◎
Core diameter	[mm]	1.6
Fibre diameter	[mm]	0.05
External diameter	[mm]	5.4
Fibre material		glass
Fibre head material		stainless steel (1.4571/316Ti)
Fibre sheath material		metal silicone
Remarks		
Pack quantity		1 pcs.