



9000 E



- 300 lb. weight capacity
- Pneumatic height adjustment
- Seat foam density: 2 ½ lb., 55 IFD
- 360° swivel
- Adjustable backrest with lumbar support
- 5 leg base in polished aluminum
- 20" Adjustable chrome footring
- Static dissipative upholstery with a resistance of 10⁵ to 10⁹ ohms
- Comply with ANSI/ESD ST12.1-2006 standards
- 12 year warranty
- Made in the USA



Model	Seat Dimensions	Back Dimensions	Seat Adjustment Height	Seat & Back Tilt	Footring
9050M-E	20"w x 18"d, 3" thick	17½"w x 16"h, 3" thick	15 ½" - 21"	No	No
9051M-E	20"w x 18"d, 3" thick	17½"w x 16"h, 3" thick	15 ½" - 21"	Yes	No
9350M-E	20"w x 18"d, 3" thick	17½"w x 16"h, 3" thick	19" - 26 ½"	No	20" Adjustable Chrome
9351M-E	20"w x 18"d, 3" thick	17½"w x 16"h, 3" thick	19" - 26 ½"	Yes	20" Adjustable Chrome
9550M-E	20"w x 18"d, 3" thick	17½"w x 16"h, 3" thick	21½" - 31½"	No	20" Adjustable Chrome
9551M-E	20"w x 18"d, 3" thick	17½"w x 16"h, 3" thick	21 ½" - 31½"	Yes	20" Adjustable Chrome
9050L-E	20"w x 18"d, 3" thick	17½"w x 19"h, 3" thick	15 ½" - 21"	No	No
9051L-E	20"w x 18"d, 3" thick	17½"w x 19"h, 3" thick	15 ½" - 21"	Yes	No
9350L-E	20"w x 18"d, 3" thick	17½"w x 19"h, 3" thick	19" - 26 ½"	No	20" Adjustable Chrome
9351L-E	20"w x 18"d, 3" thick	17½"w x 19"h, 3" thick	19" - 26 ½"	Yes	20" Adjustable Chrome
9550L-E	20"w x 18"d, 3" thick	17½"w x 19"h, 3" thick	21½" - 31½"	No	20" Adjustable Chrome
9551L-E	20"w x 18"d, 3" thick	17½"w x 19"h, 3" thick	21 ½" - 31½"	Yes	20" Adjustable Chrome

ESD Options:

CARD5S	Dual wheel hard floor casters for all models <i>(set of 5)</i>
CAPD5S	Dual wheel carpet casters for all models <i>(set of 5)</i>
CAR5E	Single rubber wheel casters for aluminum bases <i>(set of 5)</i>
IBCS-ESD	Dual wheel interval brake casters <i>(auto brake when not seated) (set of 5)</i>
A8	Adjustable arms
"02" Control	Separate seat & back tilt levers <i>(available on tilt models only)</i>
MEG	1 Mega Ohm Resistor

Colors:

Static Control Vinyl – blue, black

Static Control Fabric – slate blue, navy blue,gray, ebony