


**RF / Coaxial Cable Assembly**  
**Rear Lock IP67 N Bulkhead Jack-to-MCX Right Angle Plug**

**multicomp** PRO


**RoHS  
Compliant**



**Electrical Performance:**


Impedance	: 50Ω
Frequency Range	: DC ~ 6.0 Ghz
Working Voltage	: 170Vrms Max.
Dielectric Withstanding Voltage	: 750Vrms Max.
Insulator Resistance	: 1000MΩ Min.

**Diagram**




Sl.	Description	Qty
1	N Rear lock B/H Jack for OD 1.37mm Cable Conn	1
2	MCX R/A Plug Crimp for OD 1.37mm Cable	
3	1.37mm Black Cable	2
4	Heat Shrink Tube F32 Ø2.5mm L=15mm Colour: Black	


1 PCS/1PE BAG SIZE:4.5"x3.5"



⑥ 3.5"x4.5" PE BAG LABLE SIZE:60x40mm:



⑧ 11"x13" PE BAG LABLE SIZE:40x15mm



Newark.com/multicomp-pro  
 Farnell.com/multicomp-pro  
 Element14.com/multicomp-pro

**multicomp** PRO