


## Coaxial Panel Connector 23\_SMA-50-0-1/111\_N

### Description

Straight panel receptacle jack, flange mount

Interface standards

IEC 60169-15\_MIL-STD-348A/310\_CECC 22110



### Technical Data

#### Electrical Data

Impedance 50  $\Omega$   
Interface frequency max. 18 GHz

#### Mechanical Data

Number of matings 500  
Weight 0.0025 kg

#### Environmental Data

Operating temperature -65 °C to 125 °C  
2011/65/EU (RoHS) compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

### Related Documents

Catalogue drawing DCA-00010331

### Ordering Information

Bulk 100 pcs package 23\_SMA-50-0-1/111\_NH  
Single package 23\_SMA-50-0-1/111\_NE