

To English


Able reducer
Specification sheet

Reducer model

EVL-120B-5-K6-28GD24
 (Shaft with key)

1.Reducer specification

Ratio	5
Backlash	6 arc-min
Allowable nominal torque	120 Nm
Allowable maximum torque	240 Nm
Allowable average input speed	3000 rpm
Allowable maximum input speed	6000 rpm
Allowable radial load (Applied to the output shaft center.)	1600 N
Allowable axial load (Applied to the output side bearing.)	1900 N
Approx. weight	10.2 kg
Moment of inertia	6.61 kg-cm ²
Lubrication type	Grease
Color of the paint	Silver



*The actual appearance might be different.