

**Die, HSS G right, tol. A with spiral point and 1.75 thread chamfer**  
for universal use up to 700 N/mm<sup>2</sup>

**ORION**<sup>®</sup>

**Application:**

For cutting G (pipe) threads externally in the material groups of steel and non-ferrous metals up to a strength of 700 N/mm<sup>2</sup>.

**Execution:**

- right die, tol. A with spiral point and 1.75 pitch

**Advantage:**

- standard geometry with excellent price/performance ratio



<b>Art. no.</b>	<b>13487 010</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	13487010
<b>Thread type</b>	Pipe thread
<b>Cutting material</b>	HSS
<b>Tolerance of dies</b>	A
<b>Thread type x nominal diameter in inches</b>	G 1/8 in
<b>Number of thread starts per inch</b>	28
<b>Outer diameter</b>	30 mm
<b>Height</b>	11 mm
<b>Cutting direction</b>	Right-hand cutting
<b>Gross Weight</b>	0.041 kg
<b>Product Group</b>	1DC

**EAN**

4039247074730