

Spirit level with second vertical bubble

Model: BMI Robust



Application:

For horizontal and vertical alignment of an object



Execution:

- Model: BMI Robust
- With ultrasonically welded bubble vials and non-glare reading
- Reverse measuring possible (0.5 mm/m)
- 2 milled measuring surfaces up to 200 cm
- Solid body and shock-absorbing rubber end caps maintain high measuring precision
- Extremely torsion-resistant due to multi-chamber profile

Advantage:

- Edgeless horizontal vial for undistorted view of bubble
- Life-long high measuring accuracy (0.5 mm/m)

Art. no.	38638040
Brand	BMI
Manufacturer Part Number	638040PS
Length	400 mm
Measuring accuracy (per length)	0.5 mm/m
Harmonized System Code	90318020
Gross Weight	0.460 kg

