

Cabinet workbench, series V

Worktop: Solid beech, 4,050 mm and 12 drawers with full-extension slide



Application:

ANKE offers a wide range of high-quality workbenches, drawer cabinets and much more. See this quality for yourself - Made in Germany!

Execution:

- Robust welded sheet steel construction
- Stable bases made of square steel tube, 45 x 45 x 2 mm, with level compensation
- Drawers with 100 % full-extension slide, doors with 180° opening angle
- Can be used immediately, as it is delivered fully pre-assembled
- Plenty of space for three workstations

Advantage:

- **Long-lasting:** 60 % greater glue surface due to special longitudinal bonding of the worktop
- **Robust:** Housing components with edges folded ten times, more folding increases resilience
- **Tested:** High levels of quality and reliability



Art. no.	50201 766
Brand	ANKE
Manufacturer Part Number	999.004.0028
Number of drawers	12 PCS
Working height	900 mm
Worktop width	4050 mm
Worktop height	50 mm
Pullout type	Full extension
Worktop depth	700 mm
Colour of front	Optional
Cabinet colour	Optional
Drawer surface	0.27 m ²
With single pull-out safety brake	Yes
Levelling	Yes
Lock type	DOM® locking system
Drawer front height	6 x 180 mm, 6 x 360 mm
Surface	Powder-coated
Drawer width (inner dimension)	500 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	500 x 540 mm
Load-carrying capacity	1500 kg
Drawer depth (inner dimension)	540 mm
Load-carrying capacity per drawer	100 kg
Material of worktop	Solid beech
Central locking	Yes
Gross Weight	368.668 kg
Product Group	502

EAN

4014641012700