

Jigsaw GST 160 BCE Professional

800 watt

BOSCH

Application:

for powerful sawing in wood, aluminium and unalloyed steel

Execution:

- adjustable 3- or 4-stage saw blade oscillating device
- speed preselection
- Highly precise saw blade guide with patented double roller
- Dust extraction connection
- Parking position for rapid, one-handed saw blade changes
- Rugged magnesium baseplate

Delivery:

Saw blade T 144 DP, saw blade T 244 D, saw blade T 308 B, splinter protection, extractor adapter 1/1 L-BOXX insert, in L-BOXX 136



Art. no.	71128 143
Brand	BOSCH
Manufacturer Part Number	0601518000
Model	GST 160 BCE
Manufacturer Article Number	0601518000
Design of the handle	Stirrup handle
Max. cutting capacity of wood	160 mm
Max. cutting capacity of steel	10 mm
Max. cutting capacity in aluminium	20 mm
Min./max. idle stroke speed	800-3000 rpm
Lift height	26 mm
Power input	800 W
Weight	2.3 kg
With working lights	Yes
With electronic feedback	Yes
With rubber-coated handle	No
With soft start	No
Gross Weight	5.519 kg
Product Group	731

EAN

3165140746274