

## Compressed air mini random orbital sander set CP7200S

Excentric stroke 2.5 mm



### Application:

Ideal for repairs of small areas

### Version:

- Practical set consisting of a small pistol-grip random orbital sander and an extensive accessory kit (50- and 75-mm hook and loop fastening plates and sandpaper)
- Extremely quiet and low-vibration pistol random orbital sander with - Moulded rubber pistol grip - Robust, TPR-sheathed metal housing - Adjustable power controller - Sound-insulated exhaust duct by handle

### Advantage:

- More user comfort thanks to: - The comparatively low noise level and low vibration levels - The ergonomic and practical shape
- A wide range of applications is possible thanks to power control and extensive accessory kit

### Delivery:

incl. 1 x 50-mm and 75-mm hook and loop fastening plate; 10 x 50-mm and 75-mm sandpaper with 320, 400 and 600 grain in a rugged carrying case



<b>Art. no.</b>	<b>75032 400</b>
<b>Model</b>	CP7200S
<b>Oscillating diameter</b>	2.5 mm
<b>Max. idle speed</b>	15000 rpm
<b>Air consumption</b>	9.9 l/s
<b>Connection thread</b>	1/4 inch
<b>Sound-pressure level</b>	88
<b>Weight</b>	0.68 kg

### EAN-Code

0015451528164