


## 100pcs 3:1 Adhesive lined Color Heat shrink tube-assortment

Item No.: 1807CA005

This range is particularly suitable for hobbyists, craftsmen, field service, service workshops, electronics and the laboratory needs. 100 pieces of shrinking ratio 3:1 standard shrinking tube for a range of application diameter from 1.6 to 12.7 mm. Hot-melt adhesive lined tubing in the multi-color. The heat-shrink tubing can be used for insulation, protective covering of components, as anti-kink protection, protection against corrosion, as well as repair of cables and lines, and much more be used.



Shrinking ratio	3 : 1
Material	PE
Shrinking temperature	70°C - 125°C
Operation temperature	-40°C - 125°C
Flammability	VW-1
Tensile strength	≥ 10.4Mpa
Elongation at break	≥ 300%
Rated voltage	600V
Diselectric strength	≥ 1.5kv/mm at 30sec.
Volume resistivity	≥ 10 <sup>14</sup> Ω



set contents

Section	Heat shrink tube		Length	pcs
	Inner diameter ø	after shrink ø		
1	7.9 mm	2.7 mm	65 mm	5
2	12.7 mm	4.2 mm	95 mm	3
3	9.5 mm	3.2 mm	95 mm	4
4	6.4 mm	2.2 mm	65 mm	8
5	1.6 mm	0.5 mm	32 mm	25
6	2.4 mm	0.8 mm	32 mm	20
7	3.2 mm	1.0 mm	32 mm	20
8	4.8 mm	1.6 mm	65 mm	15