


Schraubenschlüssel

14 Ring-Maulschlüssel OPEN-BOX, lang



- DIN 3113 Form B/ ISO 7738 Form B
- Chrome-Alloy-Steel, verchromt



| Code | mm | L mm | b mm | d mm | a ₁ mm | a ₂ mm | t mm | ΔΔ g | |
|----------|----|------|------|------|-------------------|-------------------|------|------|----|
| 40100606 | 6 | 125 | 14 | 9,5 | 4,5 | 6 | 7 | 18 | 10 |
| 40100707 | 7 | 135 | 16 | 10,8 | 5 | 7 | 8 | 25 | 10 |
| 40100808 | 8 | 145 | 17,5 | 12,1 | 5 | 7 | 8 | 28 | 10 |
| 40100909 | 9 | 155 | 19 | 13,3 | 5,5 | 8 | 9 | 34 | 10 |
| 40101010 | 10 | 165 | 21 | 14,6 | 5,5 | 8 | 9 | 43 | 10 |
| 40101111 | 11 | 180 | 23,5 | 15,9 | 6 | 9 | 10 | 55 | 10 |
| 40101212 | 12 | 180 | 25,5 | 17,3 | 6 | 9 | 10 | 61 | 10 |
| 40101313 | 13 | 195 | 27,5 | 18,6 | 6,5 | 10 | 11 | 85 | 10 |
| 40101414 | 14 | 210 | 29,5 | 20,1 | 6,5 | 10 | 11 | 88 | 10 |
| 40101515 | 15 | 215 | 31 | 21,4 | 7 | 11 | 13 | 109 | 10 |
| 40101616 | 16 | 230 | 33 | 22,7 | 7 | 11 | 14 | 108 | 10 |
| 40101717 | 17 | 240 | 35 | 24,1 | 7,5 | 12 | 15 | 155 | 10 |
| 40101818 | 18 | 255 | 37 | 25,5 | 7,5 | 12 | 16 | 151 | 10 |
| 40101919 | 19 | 265 | 39,5 | 27 | 8 | 13 | 18 | 190 | 10 |
| 40102020 | 20 | 280 | 41,5 | 28,5 | 8 | 13 | 19 | 219 | 10 |
| 40102121 | 21 | 280 | 43 | 29,8 | 8,5 | 13 | 19 | 244 | 10 |
| 40102222 | 22 | 300 | 45 | 31,3 | 8,5 | 14 | 20 | 268 | 10 |
| 40102424 | 24 | 330 | 50 | 34,3 | 9,5 | 14 | 22 | 363 | 5 |
| 40102727 | 27 | 385 | 56 | 38,6 | 10,5 | 16 | 24 | 502 | 5 |
| 40103030 | 30 | 415 | 63 | 42,6 | 12 | 18 | 26 | 645 | 5 |
| 40103232 | 32 | 430 | 67 | 45,2 | 12 | 18 | 27 | 666 | 5 |
| 40103434 | 34 | 460 | 72 | 48 | 13 | 18 | 27 | 900 | 1 |
| 40103636 | 36 | 480 | 74 | 50,8 | 13 | 19 | 28 | 951 | 1 |
| 40104141 | 41 | 560 | 84 | 57,8 | 14 | 20 | 32 | 1322 | 1 |


14 Sätze Ring-Maulschlüssel OPEN-BOX, lang



| Code | Nr. | Inhalt mm | ΔΔ g |
|----------|------------------------|--|------|
| 96401008 | 14/6 ²⁾ | 10; 13; 17; 19; 22; 24 | 1175 |
| 96401009 | 14/9 ²⁾ | 10; 11; 13; 17; 19; 22; 24; 27; 30 | 2395 |
| 96401007 | 14/10 KT ¹⁾ | 8; 10; 11; 12; 13; 14; 16; 17; 18; 19 | 1235 |
| 96401006 | 14/11 | 8; 9; 10; 11; 12; 13; 14; 15; 17; 19; 22 | 1137 |
| 96401004 | 14/15 | 6; 7; 8; 9; 10; 11; 12; 13; 17; 19; 22; 24; 27; 30; 32 | 3370 |
| 96401010 | 14/15N ²⁾ | 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22; 24; 27; 30 | 3135 |
| 96401005 | 14/17 | 6; 7; 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 20; 21; 22 | 1874 |

Standardverpackung: Rolltasche mit Klettverschluss aus extrem widerstandsfähigem Textilmaterial.

ES 14/10, 6-15 mm




- 175 x 350 x 39 mm
- 10-teilig

| Code | ΔΔ g |
|----------|------|
| | g |
| 96838105 | 700 |

| Nr. | Inhalt |
|-----|---------------------------------------|
| 14 | 6; 7; 8; 9; 10; 11; 12; 13; 14; 15 mm |

ES 14/8, 16-24 mm



- 175 x 350 x 51 mm
- 8-teilig

| Code | ΔΔ g |
|----------|------|
| | g |
| 96838106 | 1820 |

| Nr. | Inhalt |
|-----|-----------------------------------|
| 14 | 16; 17; 18; 19; 20; 21; 22; 24 mm |

TCS 14/5, 17-21 mm



- 175 x 350 x 30 mm
- 5-teilig

| Code | ΔΔ g |
|----------|------|
| | g |
| 96838188 | 1065 |

| Nr. | Inhalt |
|-----|-----------------------|
| 14 | 17; 18; 19; 20; 21 mm |

TCS 14/8, 8-16 mm



- 175 x 350 x 30 mm
- 8-teilig

| Code | ΔΔ g |
|----------|------|
| | g |
| 96838189 | 660 |

| Nr. | Inhalt |
|-----|----------------------------------|
| 14 | 8; 10; 11; 12; 13; 14; 15; 16 mm |