



Nr. / No.	Länge / Length (m)
95736	0.15
95735	0.30
93922	0.60
93918	1.00
93181	1.80
93920	3.00
93921	5.00

Micro-USB Daten- und Ladekabel

- Verbinder: USB-A Stecker > Micro USB-B St.
- Innenleiter: AWG22/28
- Material: Kabelmantel: PVC  
Innenleiter: BC, CCS  
Isolierung: PVC, HDPE  
Kontakte: vernickelt  
Geflecht: AL
- Schirmung: doppelt
- USB Standard: High Speed USB 2.0
- Datenrate: max. 480 Mbit/s
- RoHS-konform

Micro USB data and charging cable

- USB-A male > Micro USB-B female
- Inner conductor: AWG22/28
- Material: Sheath: PVC  
Conductors: BC, CCS  
Insulation: PVC, HDPE  
Contacts: nickel-plated  
Braid: AL
- Shielding: double
- USB Standard: High Speed USB 2.0
- Data rate: max. 480 Mbps
- RoHS compliant

Änderungen

Datum	Name	gez.:	Datum	Name
25.02.2019	tf	gez.:	30.07.2014	tf
		gepr.:	30.07.2014	tf
		Norm:		
Änderungen vorbehalten / Subject to change				

Bezeichnung	Blatt
USB MICRO-B SCHWARZ	
Zeichnungs-Nr.:	von

