

## Product MD 325 UB2

3 mm LED indicator  
color blue

|                            |                    |
|----------------------------|--------------------|
| product-catalog            | 3 mm LED indicator |
| color                      | blue               |
| part no.                   | MD 325 UB2         |
| current [mA]               | 12-16              |
| forward voltage [V]        | 12-14              |
| wavelength                 | 555                |
| rec. mounting hole Ø [mm]  | 4.4                |
| panel thickness [mm]       | 1 .. 2             |
| operating temperature [°C] | -25 .. +80         |
| storage temperature [°C]   | -30 .. +85         |

|                               |             |
|-------------------------------|-------------|
| chip construction             | GaN         |
| forward current max. [mA]     | 25          |
| reverse voltage max. [V]      | 5           |
| luminous intensity typ. [mcd] | 30 at 15 mA |

Low cost LED indicator with ribbed nylon body for easy front panel mounting;

150 mm PVC leads \*, AWG 26, red lead, cathode lead = blue

### note

- all dimension are in millimeter
- tolerance is  $\pm 0.25$  mm unless otherwise noted
- specifications are subject to change without notice
- version 1.0

