




CABLE/100M/ PUR/4X0.34/BK

Accessories



Product characteristics

Cable

Environment

Ambient temperature [°C] -40...90

Mechanical data

Drag chain suitability

Bending radius for flexible applications: min. 10 x cable diameter  
max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s<sup>2</sup>  
Travel speed: 5 m/s<sup>2</sup>  
Bending cycles: > 5 million  
Torsional strain: ± 180 °/m

Weight [kg] 3.026

Electrical connection

Connection

PUR cable / 100 m; 4 x 0.34 mm<sup>2</sup>; Ø 4.9 mm; halogen-free

Material

core insulation: PP (polypropylene); halogen-free; outer sheath insulation: PUR; halogen-free

Sheath colour

black

**Wiring**

Core colours

BK black  
BN brown  
BU blue  
WH white

Remarks

Pack quantity [piece] 1