



FXX*1) SOGY*2)

e.g. F09SOG1

*1) xx No. of contacts 09, 15, 25 or 37
 *2) y for performance classes 1, 2 or 3
 (contact cycle for G1/G2/G3 = 500/200/50)

xx	A [mm]	B [mm]	C [mm]
09	30.8	16.4	25
15	39.1	24.7	33.3
25	53	38.5	47.04
37	69.3	54.9	63.5

RoHS compliant

3	xx	Signal contact	S0 / Brass	AWG 20 / G1/G2/G3
2	1	Shell	Steel	tin plated
1	1	Insulator	PBT (-55°C - +125°C)	white
	No. St.	Part	Surface plating/Colour/Class	

Measurement without tolerance		SCALE	TITLE
Reference acc. to ISO 2768-m		2:1	
NAME / DATE	Denzinger		
DRAWN	08-10-2002		
CHECKED	flößmann		
	08-10-2002		

D-Sub Miniature Connector

1	REV.	DATE	CH.-NO.	DWG.NO.	REV.	PAGES
				FxxSOGy	1	1



ORIGINAL DIN A3 DRAWING AS A FILE

REPLACEMENT FOR:

FxxSOGy a

1