

Product information

37 23 125

Flat Nose Pliers

For precision mechanics

DIN ISO 9655

- Precision pliers for fine assembly work, e.g. in electronics and fine mechanics
- For gripping, holding, bending and adjusting
- Tips precision-ground
- Smooth gripping surfaces
- Edges carefully deburred
- Lap joint
- Flat, concave and pointed jaws
- High-grade special tool steel, forged, oil-hardened




General

Article No.	37 23 125
EAN	4003773043645
Pliers	chrome-plated
Head	chrome-plated
Handles	plastic coated
Weight	72 g
Dimensions	125 x 49 x 12 mm
Standard	DIN ISO 9655
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Jaw thickness (joint) (D)	7.0 mm
Tips width (E)	2.0 mm
Tips thickness (F)	2.0 mm
Jaw length (B)	27.0 mm
Head width (A)	12.5 mm



technical change and errors excepted