

# IN 19 5

## Screwdriver bit socket 1/2"

for in-hex screws

|                    |  |
|--------------------|--|
| Code               | ETIM   |
| 6153150            | EC002157 Innensechskant-Einsatz für Steckschlüssel |
| EAN                | UNSPSC   |
| 4010886615317      | 27-11-17-01 Schraubendreher                        |
| Country of Origin  | eCl@ss   |
| Germany            | 21-04-04-02 Schraubendrehereinsatz                 |
| Customs tariff no. |  |
| 82079030           |  |



### Article description

- Square drive as per DIN 3120 - C 12.5, ISO 1174, with ball retaining groove
- Hand-operated, knurled grip
- Chrome-plated
- With pressed-in pin in GEDORE vanadium special steel, manganese-phosphated
- IN 19 17 for oil filter and drain plug screws
- \* not standardised

### Article information

|                              |                       |  |                  |
|------------------------------|-----------------------|--|------------------|
| Contents (Qty of pieces)     | 1 tlg.                | Drive connector square female (metric) | 12,5 mm          |
| Total length [mm]            | 61 mm                 | Total width [mm]                       | 23 mm            |
| Total height [mm]            | 23 mm                 | Drive connector square female [inch]   | 1/2"             |
| Net weight [kg]              | 0,069 kg              | Working length                         | 38,0 mm          |
| Material                     | Chrome-vanadium steel | Tip length                             | 22,0 mm          |
| Width across flats 1 [mm]    | 5                     | Standard                               | not standardised |
| Surface                      | chrome-plated         | Insert Ø Actuator                      | 22,5 mm          |
| REACH registration available | 0                     |  |                  |